

Project Name

Location

Prepared By



Notes

[www] 11-25-2021 04:01:41

General

Status	Active
Finish	White
Wattage	10W
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White/Color Changeable
Width (in.)	5.31
Height (in.)	1.50
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

Specifications

Technology	LED
CRI	90
Lumen Output	650L
Rated Hours	25000
Voltage	120V
Dimmable	Yes-Dimmable
Beam Angle	110
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
IC Rated	Yes
Weight (lb.)	0.81
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Remote Driver LED Downlight

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Pending
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - 3 hr per day
----------	-------------------------------