

Project Name

Location

Prepared By



Notes

[www] 11-25-2021 04:01:41

General

| | |
|---------------------------|-------------------------------------|
| Status | Active |
| Finish | White |
| Wattage | 12W |
| CCT (Kelvin) | 2700K-5000K |
| Color Temperature | Warm to Cool White/Color Changeable |
| Width (in.) | 7.20 |
| Height (in.) | 1.50 |
| Indoor or Outdoor Fixture | Indoor |

Smart Product Info

| | |
|----------------------------|--|
| IOT Enabled | Yes |
| Voice Assistants Supported | Siri Shortcuts; Alexa; Hey Google; SmartThings |

Specifications

| | |
|-----------------------|---|
| Technology | LED |
| CRI | 90 |
| Lumen Output | 850L |
| Rated Hours | 25000 |
| Voltage | 120V |
| Dimmable | Yes-Dimmable |
| Beam Angle | 110 |
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |
| IC Rated | Yes |
| Weight (lb.) | 1.03 |
| Fixture Shape | Round |
| Fixture Material | Steel |
| Fixture Type | Remote Driver LED Downlight |

Compliance

| | |
|--------------------|--------------------------|
| Safety Listing | cETLus |
| Location Rating | Wet |
| Energy Star | Pending |
| California Status | California T24 Compliant |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |

Additional Information

| | |
|----------|-------------------------------|
| Warranty | 5 Year Limited - 3 hr per day |
|----------|-------------------------------|