

2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- 1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- 2. DIMENSIONS IN [ ] ARE METRIC.
- 3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- 4. WEIGHT: 32.7oz/EACH [ 927.1g/EACH ]

POEXKIT1 CONSISTS OF:

QTY	PANDUIT PART NUMBER	DESCRIPTION
1	POEXTX1	PoE EXTENDER 1-PORT TRANSMITTER
1	POEXRX1	PoE EXTENDER 1-PORT RECEIVER
1	POWER-60W	60 WATT AC-DC POWER SUPPLY. IN: 100-264VAC 50/60HZ, IEC60320 C14 MALE INLET OUT: 55VDC+/-5% 1.1A MAX, CORD WITH 2.1x5.5MM PLUG
1	C13CORD-B	6FT (1.8M) LONG CORD WITH IEC60320 C13 FEMALE PLUG ON ONE END 3-PRONG NEMA 5-15M PLUG ON THE OTHER END PLUGS INTO USA AND LATAM TYPE OUTLETS AND POWER-60W (ABOVE)

PART NUMBER		<b>POEXKIT1</b>	
TITLE		<b>1-PORT PoE EXTENDER KIT</b>	
CUSTOMER DRAWING			
ITEM REVISION NAME		00240NAD/01	
DATASET FILE NAME		00240NAD_DC/00C	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE BOM	
DRAWING NUMBER		00240NAD-DC	
DRAWN BY	DATE	CHK	SCALE
BJN	10-16-18	SGO	NONE
SHEET 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00C	5-3-20	BJN	SGO	TAM	POWER SUPPLY AND CORD PN ADDED, NOW THEY ARE ASSIGNED.	00240NAD-DC
00B	9-4-19	BJN	SGO	AMN	WEIGHT WAS 32.36)z/EACH [917.3g/EACH]	00240NAD-DC
00A	10-16-18	BJN	SGO	SRSE	RELEASED TO PRODUCTION	00240NAD-DC

2

1

A-SIZE CUSTOMER

A

A

B

B