

Features and Benefits

- Recessed generator receptacle
- G90 Galvanized steel with superior electro-deposition paint finish provides excellent corrosion protection
- All in one construction for factory assured terminations
- Rolled edge door for cord protection
- Cover design allows cords to exist while maintaining the NEMA 3R integrity
- Padlockable door to help prevent unauthorized access
- Deadfront construction prevents accidental contact with live parts
- UL listed
- Blank top – no hub provision





FIG.	UL	MODEL NUMBER	RECEPTACLES	AMPS	VOLTS	HEIGHT	WITDTH	DEPTH
A	Y	U020N	L14-20	20	120/240	14-3/8"	6-3/4"	5-3/16"
B	Y	U030N	L14-30	30	120/240	14-3/8"	6-3/4"	5-3/16"
C	Y	U050N	CS6375 **	50	120/240	14-3/8"	6-3/4"	5-3/16"
D	Y	U022N	(2) L14-20 *	40	120/240	14-3/8"	6-3/4"	5-3/16"

* U022N also has (2) CB120 circuit breakers and one breaker space.

** CS6375 is a California Standard, 3-pole / 4-wire grounded non-NEMA.

Knockouts



G = 1/2", 3/4", 1"

S = 1/2", 3/4", 1", 1-1/4", 1-1/2"