



BURNDY Catalog Number
UPC Number
Description
Status

YAV28LTC14FX
7818100220233
CU. COMP.1 HOLE 4/0 FX
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
Strip Length

Dimensional

Straight
2.23
Chamfered
0.27
Standard
0.15
1.03
1.14
1-1/16

Number of Holes

General

1
Cu Comp Terminal Flex Cond, Bvl
Entry, 1 Hole/W/InspWindow, 4/0
Weld, 4/0(550/#24)DLO Flex, 4/0
AWG Code, 200 Navy, 600 V-35
kV, 1/4" Stud, Std bbl

Product Description

Conductor(s)

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

4/0 AWG
4/0 AWG
4/0 AWG
N/A
4/0 (550/#24) DLO
4/0 AWG

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Physical

Tin
1/4
Purple
Y
15
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175