



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YAV4CL2TC38FX  
 7818100221911  
 CUHYLUG 4STRFLEX 2)3/8 4  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tongue Angle	Straight
Length (in)	2.68
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.08
B Length (in)	0.50
Pad Width (in)	0.58
E - in	1.00
Strip Length	9/16

**General**

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/ Inspection Window, 4 Flex, 3/8" Stud, 1" Stud Hole Spacing, Short Barrel, Tin Plated

**Conductor(s)**

Flex (Class G) Size - Range	4 AWG
Flex (Class H) Size - Range	4 AWG
Flex (Class I) Size - Range	4 AWG
Copper Solid Size (Range)	4 AWG
DLO Size (Range)	5 (91/#24) DLO-4 (105/#24) DLO
Copper Stranded (Range)	4 AWG

**Physical**

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Gray
Plated (Yes or No)	Y
Index Number	8
Product Material	Copper

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175