

YC4C8

by Burndy
Catalog ID: YC4C8

Prop 65 Notice

CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, Run: 6 Sol. - 4 Str., Tap: 8 Sol. - 8 Str.

Features: Range-Taking Connector: Lowers Inventory Requirements, Compact Size: Easy To Tape And Insulate Connection, Manufactured From High Conductivity Wrought Copper: Provides Low Resistance And Excellent Electrical Conductivity, Economical: Provides Low Installed Cost, 8A - Use CRIMPITS Accommodating 6 Stranded Copper, 6A - Use CRIMPITS Accommodating 4 Stranded Copper, 4A - Use CRIMPITS Accommodating 2 Stranded Copper, 2A - Use CRIMPITS Accommodating 1/0 And 2/0 Copper, Use PUADP-1 Adapter When Using U Dies In The Y46 HYPRESS, Tools, Die Set Catalog Number, And (number Of Crimps): MD6 Tool, W-BG Die, (1), BG Die, (2), OUR840 Tool, XNBS Die, (2), Y35, Y750, Y45 Tool, U-BG Die, (1), Y46 Tool, U-BG Die With PUADP-1 Adapter, (1), Die Index: BG Element A, Conductor Type: Run: Commercial Stranded Copper, Tap: Commercial Stranded Copper, Conductor Size (run - Range): 6 - 4 AWG, Conductor Size (tap Range): 8 - 2 AWG, Shape: C



Product Details

General

Application	For Making Tap Or Parallel Copper Connections
Die Index	BG or 5/8
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810114254
UPC 12 Digit	7818101142544

Dimensions

Dimension - Height inch	0.73 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in

Conductor Related

Conductor - Copper Solid Run Range	6 Sol. - 4 Str.
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Str Run Range	6 Sol. - 4 Str.
Conductor - Copper Str Tap	8 AWG
Conductor Type	Cu C Sol-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)