



YC26C26

by Burndy Catalog ID: YC26C26

Prop 65 Notice

CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, 1/0 Str. - 2/0 Str. (Run & Tap).

Features: Range-Taking Connector: Lowers Inventory Requirements, Compact Size: Easy To Tape And Insulate Connection, Manufactured From High Conductivity Wrought Copper: Provides Low Resistance And Excellent Electrical Conductivity, Economical: Provides Low Installed Cost, 8A - Use CRIMPITS Accommodating 6 Stranded Copper, 6A - Use CRIMPITS Accommodating 4 Stranded Copper, 4A - Use CRIMPITS Accommodating 2 Stranded Copper, 2A - Use CRIMPITS Accommodating 1/O And 2/O Copper, Use PUADP-1 Adapter When Using U Dies In The Y46 HYPRESS, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750, Y45 Tool, U-O Die, (1), U-E Die, (3), Y46 Tool, U-O Die With PUADP-1 Adapter, (1), U-E Die With PUADP-1 Adapter, (3), Die Index: O Element A, Conductor Size (run - Range): 1/O - 2/O AWG, Conductor Type: Run: Commercial Stranded Copper, Tap: Commercial Stranded Copper, Shape: C, Conductor Size (tap Range): 1/O - 2/O AWG

Product Details

General

| Application | For Making Tap Or Parallel Copper Connections |
|--------------|---|
| Die Index | E or O |
| Material | Copper |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | CRIMPIT |
| Trade Name | CRIMPIT™ |
| Туре | YC-C Series |
| UPC | 781810115305 |
| UPC 12 Digit | 7818101153055 |

Dimensions

| Dimension - Height inch | 1.35 in |
|---------------------------------|---------|
| Dimension - L Length Overall mm | 23 mm |
| Dimension - Length Overall inch | 0.92 in |

Conductor Related

| Conductor - Copper Str Run Range | 1/0 AWG-2/0 AWG |
|----------------------------------|-----------------|
| Conductor - Copper Str Tap Range | 1/0 AWG-2/0 AWG |

Certifications and Compliance

| Certification - CSA Approved | No |
|-------------------------------|----|
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |

| Industry Standard(s) | • UL 486A • UL486B |
|------------------------------------|-----------------------|
| Standards - Industry Standards Met | • UL 486A • UL486B |
| Standards - RoHS Compliance Status | СМ |
| UL Listed | Yes |

Logistics

| Minimum Pack Quantity | 1 |
|-----------------------|---|
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)