



BIBS3503

by Burndy
Catalog ID: BIBS3503

Prop 65 Notice

Aluminum Multiple Tap Connector, Clear Insulated, 3 Port, 1 Sided Entry, 10 AWG-350 kcmil, Al/Cu Rated.

Features: UNITAP Rated For Code Conductor Only, Torque: 275 IN-LB, Wire Entry: Single, Hex Size (key): 5/16 IN, Conductor Size (run - Range): 10 AWG - 350 KCMIL, Type Of Insulation: Plastisol, Wire Strip Length: 1-1/8 IN, Number Of Ports: 3

Product Details

General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	3
Physical Attribute - Number of Screws	10
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810131770
UPC 12 Digit	7818101317700

Dimensions

Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	80 mm
Dimension - Length Overall inch	3.13 in
Dimension - Width inch	2.32 in
Dimension - Width mm	59 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	10 - 350 Str
Conductor - Copper Str Size Range	10 - 350 Str

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)