

YPC26R8U

by Burndy
Catalog ID: YPC26R8U



Compact compression connector designed to tap small lighting wires from secondaries. Figure 6-shape separates run and tap, and minimizes galvanic corrosion

Features: Compact Compression Connector Designed To Tap Small Lighting Wires From Secondaries, Figure 6 -Shape Separates Run And Tap, And Minimizes Galvanic Corrosion, Connector Can Be Gripped In Tool And Slipped Over Line For Easier Installation, Pre-Filled With PENETROX Joint Compound And Stripsealed, Conductor Type: ACSR, Compressed ACSR, Aluminum And Copper, Compressed Aluminum, Shape: 6, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-O Die, (2), Y35, Y750 Tool, U-O Die, (1), Y45 Tool, U-O Die With PT-6515 Adapter, (1), Y46 Tool, U-O Die With PUADP-1 Adapter, (1), OUR840 Tool, W-O Die, Die Index: 0 Element A

Product Details

General

Application	For Combinations Of Copper, Aluminum, ACSR, Compressed And Compact Conductors
Die Index	O
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-R-U
UPC	781810137376
UPC 12 Digit	7818101373766

Dimensions

Dimension - Height inch	1.30 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in
Dimension - Width inch	0.73 in

Conductor Related

Conductor - ACSR Str Run	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Run Range	2 (6/1) Sparrow AWG-3/0 (6/1) Pigeon AWG
Conductor - AL Str Run	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Run Range	1 AWG-3/0 AWG
Conductor - AL Str Tap	8 AWG
Conductor - Copper Solid Run	18 AWG
Conductor - Copper Solid Tap	14 AWG
Conductor - Copper Str Run	1 AWG;1/0 ;2/0 AWG;3/0 AWG

Conductor - Copper Str Run Range	1 AWG-3/0 AWG
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	14 AWG-8 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)