



BURNDY Catalog Number
UPC Number
Description
Status

YPC33R26U
 7818101375055
 397-556R 6-2/0T AL/CU/AC
 Active

Web Use
 BURNDY Product Line

Length (in)

Dimensional
 2.125

Product Description

General
 Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu:250 (37) - 400 (37)

ACSR Compact Tap (Range)
 ACSR Tap Size (Range)
 Aluminum Run Size (Range)
 AAAC 5005 Tap (Range)
 Copper Tap Range
 ACSR Run Size (Range)
 Copper Stranded Run (Range)
 ACSR Compact Run (Range)
 Aluminum Tap Size (Range)
 AAAC 5005 Run (Range)
 ACAR Tap Size (Range)
 ACAR Run Size (Range)

Conductor(s)
 6 AWG-1/0 AWG
 N/A
 250 kcmil-400 kcmil
 30.58 (7) kcmil-123.3 (7) kcmil
 6 AWG-2/0 AWG
 N/A
 250 kcmil-400 kcmil
 266.8 kcmil-336.4 kcmil
 6 AWG-2/0 AWG
 312.8 (19) kcmil-465.4 (19) kcmil
 N/A
 N/A

Index Number

Physical

N

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

N
 N
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175