

YSS4R

by Burndy
Catalog ID: YSS4R

Prop 65 Notice

Single aluminum sleeve designed for service drop or short span overhead distribution lines.

Features: Single Aluminum Sleeve Designed For Service Drop Or Short Span Overhead Distribution Lines, Installed With OH25 One-Hand Tool, And Other Standard Tooling, Pre-Filled With PENETROX Joint Compound And Color Coded Capped, Holding Strength: ACSR: 1000 LB, Aluminum: 800 LB, Oh25 Application: Conductor, (indentd Per End): Aluminium: 4 AWG (7), (3), 2 AWG Solid, (3), 4 AWG - 5005 KCMIL, (3), ACSR: 4 AWG (6-1), (7-1), (3), Die Index: BG Element A, Conductor Type: ACSR, Aluminum, Color Code: Orange, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-BG Die, (3), BG Die, (6), Y35, Y750 Tool, U-BG Die, (3), Y45 Tool, U-BG Die With PT-6515 Adapter, (3), Y46 Tool, U-BG Die With PUADP-1 Adapter, (3)



Product Details

General

| | |
|---------------------------|---|
| Application | For Aluminum, ACSR, 6201, 5005 And Compressed Conductors And Service Drop Or Short Span Overhead Distribution Lines |
| Color Code | Orange |
| Connector Type | Splice |
| Die Index | BG or 5/8 |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | HYSPLICE |
| Trade Name | HYSPLICE™ |
| Type | YSS |
| UPC | 781810169650 |
| UPC 12 Digit | 7818101696500 |

Dimensions

| | |
|-----------------------------------|------------|
| Dimension - B Length fraction | 1-39/50 in |
| Dimension - B Length inch | 1.78 in |
| Dimension - L Length Overall mm | 96 mm |
| Dimension - Length Overall inch | 3.78 in |
| Dimension - Outside Diameter inch | 0.65 in |

Conductor Related

| | |
|---------------------------------|--------------------------------------|
| Conductor - ACSR Str Size | 4 (6/1) Swan AWG;4 (7/1) Swanate AWG |
| Conductor - ACSR Str Size Range | 4 (6/1) Swan AWG-4 (7/1) Swanate AWG |
| Conductor - AL Str Size | 4 AWG;3 AWG;2 AWG |
| Conductor - AL Str Size Range | 4 AWG-2 AWG |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)