



BIBS43

by Burndy
Catalog ID: BIBS43

Prop 65 Notice

Aluminum Multiple Tap Connector, Clear Insulated, 3 Port, 1 Sided Entry, 14-4 AWG, Al/Cu Rated.

Features: UNITAP Rated For Code Conductor Only, Torque: 45 IN-LB, Wire Entry: Single, Hex Size (key): 1/8 IN, Conductor Size (run - Range): 14 - 4 AWG, Wire Strip Length: 5/8 IN, Number Of Ports: 3, Type Of Insulation: Plastisol

Product Details

General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Hex Key	1/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	3
Physical Attribute - Number of Screws	3
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810223826
UPC 12 Digit	7818102238266

Dimensions

Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.51 in
Dimension - Screw Size inch	1/4
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Size Range	14 - 4 Str
Conductor - Copper Str Size Range	14 - 4 Str
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)