



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GD1729  
7818102603022  
2/0SOL-250, 1 1/2 IPS,  
Active

**Web Use**  
BURNDY Product Line

**Dimensional**

Width (in) 3.25  
Height (in) 4.00  
Size (Hex) or Size (Bolt) 3/8  
Size (Hex) or Size (Bolt) - in 0.38  
Width (Fraction) 3-1/4  
Height (Fraction) (in) 4

**General**

Product Description Mechanical Grounding Connector,  
2 Cables to Rod or Tube, 2/0 AWG  
(Sol) -250 kcmil, 1-1/2" Pipe, 1-  
5/8" -1-7/8" Rod

**Conductor(s)**

Copper Tube Size (SCH40) - Range 1-5/8-1-7/8  
Rod Size (Range) 1 5/8 in-1 7/8 in  
Copper Solid Size (Range) 2/0-4/0  
Copper Stranded (Range) 2/0-250

**Physical**

Installation Torque 240  
Type of Plating Unplated  
Plated (Yes or No) N  
Product Material Copper Alloy

**Approvals / Certifications**

UL Listed Y  
CSA Certified N  
ROHS Compatible Exempt  
UL Recognized N  
CULUS N  
Industry Standards UL467  
Rated for Direct Burial Y

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175