

MD68

by Burndy
Catalog ID: MD68

Prop 65 Notice

Hand Operated Tool, 9000 lbs, Installs full range of connectors (taps, splices, terminals): #14 through 4/0.

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Features: Proper Crimps Are Assured With Butting Steel Jaws, No Additional Dies Required For O And D3 Size Tap Connectors, Increased Strength And Greater Bearing Area Is Provided With Larger Steel Bolts, Fast, Easy, One-Hand Die Insertion, No Lost Dies With Spring Loaded Positive Lock Die Retainer Buttons, Easy Visual Field Check For Proper Tool Adjustment With Orange Alignment Guide Lines, Over 90,000 Crimps Provided With Teflon Impregnated Steel Backed Bronze Bushings, Full Crimp Force Assured With Over Center Cam Action, Easy Tool Adjustment With Allen Wrench, Operator Protection Provided With Butt Stops And Heat Shrink Tubing, Long Life Expectancy Provided With Select Clear Hickory Handles And Lightweight High Strength Aluminum Alloy Castings, Easier Tool Operation Is Provided With Bent Handles And Anti-Slip Grips, The D3 Groove Accommodates The Complete Line Of Type W Die Inserts, 5-year limited warranty, Conductor Type: ACSR, 6201, 5005, Aluminum, Copper, Copperweld, Alumoweld, Steel, Compressed And Compact Conductors, Covered Handles: Yes, Permanent Dies: Yes, Dies Used: W, X And W VT, Weight: 6 LB, Accepts Dies: Yes, Fully Covered: No, Cutting Dies Available: Yes 5 year limited warranty



Product Details

General

Application	Crimping
Die Type	W & X dies
Sub Brand	HYTOOL
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810446553
UPC 12 Digit	7818104465533

Dimensions

Length	25.38 in
Weight	6 lb
Width	7.04 in

Conductor Related

Crimping Ranges	Copper: 10 sol. - 500 Kcmil; Copper Flex: #8 to 350 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)