



OH25

by Burndy
Catalog ID: OH25

Prop 65 Notice

One-Hand operation, Dieless, Full cycle Ratchet Tool, 6000 lbs, #10 through 1/0.

- Heat treated steel
- 1/4" hole for snap fastener
- Forged steel jaws
- Nest die
- Comfort grip handles
- Spring loaded handles
- Protected ratchet mechanism
- Replacement stainless steel indentor

Features: One Crimp Speeds Installation, No Dies To Lose, Long Dependable Life With Forged Steel Jaws And Stainless Steel Indentor, Convenient Hole To Hang Tool, Protection Of Internal Parts Provides Long Life, Ratchet Mechanism Provides Proper Crimp And Uniform Quality Installations, Easy One-Hand Tool Operation With Spring Loaded Comfort Grip Handles, Proven Reliable With Years Of Dependable Service, 5-year Limited Warranty, Accessories: Leather Holster: PT4583, No-Go Gauge: PT8504, The PT8504 NO-GO Gauge Is Used To Check The OH25 HYTOOL Crimp Dimensions, Wire Stripper: No, Weight: 2.11 LB, Wire Cutter: No, Dieless: Yes, Crimps Coaxial Connectors: No 5 year limited warranty

Product Details

General

Application	Crimping
Die Type	Dieless
Sub Brand	HYTOOL
Tool Type	Dieless Full Cycle Ratchet
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810452004
UPC 12 Digit	7818104520044

Dimensions

Height	1.30 in
Length	12.00 in
Weight	2.687 lb
Width	3.75 in

Conductor Related

Crimping Ranges	Aluminum: #10 AWG - #1/0 AWG
-----------------	------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)