



YA444N

by Burndy
Catalog ID: YA444N

Prop 65 Notice

Copper Compression Lug, 4 Hole w/o Inspection Window, 1000 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel, Tin Plated.

Features: 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight, Color Code: White, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y46 Tool, P44RT Die, Die Index: 27, Wire Strip Length: 3-1/16 IN

Product Details

General

Application	For Code Conductor
Color Code	White
Connector Type	Terminal
Die Index	27
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810524015
UPC 12 Digit	7818105240155

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2 in
Dimension - D inch	3.02 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	181 mm
Dimension - Length Overall inch	7.14 in
Dimension - N inch	0.63 in

Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	3.00 in
Dimension - Strip Length inch	3-1/16 in
Dimension - Stud Size inch	1/2 in
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	1000 kcmil
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)