

YS39

by Burndy
Catalog ID: YS39

Prop 65 Notice

Copper Compression Splice, 750 kcmil, 6.38" Splice Length, Long Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 Volts to 35 kV, Long Barrel Length: Ideal For 600 Volt Heavy Duty Applications, Also May Be Used At Higher Voltages Up To 35KV, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Much Greater Mechanical And Electrical Properties, Color Code: Black, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (4), Oil Stop: No, Tapered End: No, Die Index: 24 Element A, Conductor Type: Commercial Stranded Copper, Wire Strip Length: 2-15/16 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750 Tool, U39RT Die, (4), Y46 Tool, U39RT Die With PUADP-1 Adapter, (4)



Product Details

General

| | |
|------------------------|---|
| Application | For Heavy Duty Applications And Used At Higher Voltages Up To 35 KV |
| Color Code | Black |
| Connector Type | Splice |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Long |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLINK |
| Trade Name | HYLINK™ |
| Type | YS, Long Barrel |
| UPC | 781810526859 |
| UPC 12 Digit | 7818105268599 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 2.81 in |
| Dimension - L Length Overall mm | 162 mm |
| Dimension - Length Overall inch | 6.38 in |
| Dimension - Strip Length inch | 2-7/8 |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------|-----------|
| Conductor - Copper Str Size | 750 kcmil |
|-----------------------------|-----------|

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)