



## PENA138

by Burndy  
Catalog ID: PENA138

Oxide Inhibiting Electrical Joint Compound, 8 OZ, For Al-Al, Al-Cu & Al Conduit Threads / Insulated Cable.

consists of a non-petroleum base vehicle in which zinc particles are suspended,UL Listed and recommended for all voltages

## Product Details

### General

Application	Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper
Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Squeeze Bottle
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592571
UPC 12 Digit	7818105925711
Viscosity at 100 Fahrenheit	250 °F

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Container Size	8 oz
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)