



YS31A1

by Burndy Catalog ID: YS31A1

Prop 65 Notice

Aluminum Compression Splice, 350 kcmil, 4.04" Splice Length, Long Barrel, Belled End, Tin Plated.

Features: Manufactured From High-Conductivity Wrought Aluminum With Heavy Duty Wall Thickness: Provides High-Conductivity/Low Resistance And Ductility For An Excellent Combination Of Electrical And Crimp Forming Properties, Electro-Tin Plated: Provides Durable Long Lasting Corrosion Resistance, Internally Bevelled Barrel: Provides Easy Cable Entry, Solid Center Stop And Prefilled With PENETROX Oxide Inhibiting Compound: Provides Stop For Proper Conductor Insertion And An Aid In Forcing The PENETROX Between The Individual Wire Strands, Color-Coded End Caps: Provides Easy Wire Size And Die Code Identification Plus Prevents Foreign Materials From Entering And Contaminating The Connector Prior To Usage, Connector Is Clearly Marked With Wire Size, Die Index And The Proper Number And Location Of Crimps: Provides Easy Identification And Tooling Recommendation, Proper Compression Forms A Homogeneous Mass Resulting In An Excellent Electrical Connection, UL Listed for Aluminum only, Dieless Tools (number Of Crimps): Hydraulic HYPRESS: Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (3), Color Code: Brown, Die Index: 299 Element A, Wire Strip Length: 2-1/8 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y75 Tool, U31ART Die, (2), Y46 Tool, U31ART Die With PUADP-1 Adapter, (2), Conductor Type: Stranded Aluminum Or Copper

Product Details

General

Application	For Use On All Combinations Of Aluminum To Aluminum, Aluminum To Copper, And Copper To Copper Conductor Combinations
Color Code	Brown
Connector Type	Splice
Die Index	299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Temperature Rating	194
Trade Name	HYLINK™
Туре	YS-A, Standard Barrel
UPC	781810757499
UPC 12 Digit	7818107574999

Dimensions

Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.89 in
Dimension - L Length Overall mm	103 mm

Dimension - Length Overall inch	4.04 in
Dimension - Outside Diameter inch	1.11 in
Dimension - Strip Length inch	2-1/8 in
Length	4.04 in
Outside Diameter	1.11 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil
Conductor - Copper Str Compact Size	350
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

Minimum Pack Quantity	1	
-		

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)