



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YCS25R  
7818108205133  
1/0 AL JUMPER,0.621 IN OD  
Active

**Web Use**  
BURNDY Product Line

B Length (Fraction)  
Length (in)  
B Length (in)  
Length (Fraction)

**Dimensional**  
3-12/25  
7.09  
3.48  
7-1/8

Product Description

**General**  
HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 7-1/8 IN L Y

Prefilled (Oxide Inhibitor)

**Conductor(s)**  
1/0 (6/1) Raven AWG  
1/0 AWG  
123.3 (7) kcmil  
1/0 AWG  
123.3 (7) kcmil

ACSR Size (Range)  
ACSR Compact Size (Range)  
AAAC 6201 Size (Range)  
Aluminum Size (Range)  
AAAC 5005-Size (Range)

**Physical**  
Jumper  
Unplated  
N  
243  
Aluminum

Type of Splice  
Type of Plating  
Plated (Yes or No)  
Index Number  
Product Material

**Approvals / Certifications**  
N  
N  
Compliant  
N  
N  
RUS

UL Listed  
CSA Certified  
ROHS Compatible  
UL Recognized  
CULUS  
Industry Standards

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175