



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YDS4RL  
7818108206433  
4 ACSR 1 PIECE SPLICE,11.06 In L  
Active

**Web Use**  
BURNDY Product Line

B Length (Fraction)  
Length (in)  
B Length (in)  
Length (Fraction)

**Dimensional**  
11-3/50  
11.06  
11.06  
11-7/8

**Product Description**

**General**  
AL Overhead Compression Splice -  
Single Sleeve Full Tension,  
Accommodates: AAC, ACSR and  
AAC, 11-7/8 IN L  
Y

**Prefilled (Oxide Inhibitor)**

**Conductor(s)**  
4 (6/1) Swan AWG-4 (7/1)  
Swanate AWG  
N/A  
48.69 (7) kcmil  
4 AWG  
48.69 (7) kcmil

ACSR Size (Range)  
ACSR Compact Size (Range)  
AAAC 6201 Size (Range)  
Aluminum Size (Range)  
AAAC 5005-Size (Range)

**Physical**  
Unplated  
N  
BG,243,687  
Aluminum

Type of Plating  
Plated (Yes or No)  
Index Number  
Product Material

**Approvals / Certifications**  
N  
N  
Compliant  
N  
N

UL Listed  
CSA Certified  
ROHS Compatible  
UL Recognized  
CULUS

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175