

YDS2C

by Burndy
Catalog ID: YDS2C

Prop 65 Notice

CU Full tension splice, Index: 163.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 163 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W163 Die, (6), Y35, Y750 Tool, U163 Die, (2), Y45 Tool, U163 Die With PT-6515 Adapter, (2), Y46 Tool, U163 Die With PUADP-1 Adapter, (2), Conductor Type: Stranded Copper



Product Details

General

| | |
|---------------------------|--------------------------------|
| Application | For Stranded Copper Conductors |
| Connector Type | Splice |
| Die Index | 163 |
| Material | Copper |
| Oxide Inhibitor Type | Penetrox E |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | HYSPLICE |
| Trade Name | HYSPLICE™ |
| Type | YDS - C |
| UPC | 781810820902 |

Dimensions

| | |
|-----------------------------------|------------|
| Dimension - B Length fraction | 1-18/25 in |
| Dimension - B Length inch | 1.72 in |
| Dimension - L Length Overall mm | 94 mm |
| Dimension - Length Overall inch | 3.69 in |
| Dimension - Outside Diameter inch | 0.50 in |

Conductor Related

| | |
|-----------------------------|-------|
| Conductor - Copper Str Size | 2 AWG |
|-----------------------------|-------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)