



BURNDY Catalog Number YDS321RL
UPC Number 7818108210399
Description 336 ACSR 1 PIECE SPLICE,OD:1.13 IN
Status Active

Web Use
 BURNDY Product Line

| Dimensional | |
|-----------------------------|--|
| B Length (Fraction) | 9-3/50 |
| Length (in) | 18.25 |
| B Length (in) | 9.06 |
| Length (Fraction) | 18-1/4 |
| General | |
| Product Description | AL Overhead Compression Splice - Single Sleeve Full Tension, Accommodates: AAC, ACSR and AAC, Die Index: 655 |
| Prefilled (Oxide Inhibitor) | Y |
| Conductor(s) | |
| ACSR Size (Range) | 336.4 (18/1) Merlin |
| ACSR Compact Size (Range) | N/A |
| AAAC 6201 Size (Range) | N/A |
| Aluminum Size (Range) | 336.4 |
| AAAC 5005-Size (Range) | N/A |
| Physical | |
| Type of Plating | Unplated |
| Plated (Yes or No) | N |
| Index Number | 655 |
| Product Material | Aluminum |
| Approvals / Certifications | |
| UL Listed | N |
| CSA Certified | N |
| ROHS Compatible | Compliant |
| UL Recognized | N |
| CULUS | N |
| Documentation | |

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175