



BURNDY Catalog Number
UPC Number

WCY64
 7818108746088
 Wejtap, .940 D Max(Run), .650 D
 Max.(TAP)
 Active

Description
Status

Web Use
 BURNDY Product Line

General	
Product Description	Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.421 (Max), 1.216 (Min)
Conductor(s)	
AAAC 6201 Tap (Range)	N/A
ACSR Tap Size (Range)	1/0 (6/1) Raven AWG-300.0 (26/7) Ostrich kcmil
Aluminum Run Size (Range)	350 kcmil-700 kcmil
AAAC 5005 Tap (Range)	N/A
Copper Tap Range	N/A
ACSR Run Size (Range)	336.4 (18/1) Merlin kcmil-556.5 (30/7) Eagle kcmil
Copper Stranded Run (Range)	N/A
AAAC 6201 Run (Range)	N/A
Aluminum Tap Size (Range)	2/0 AWG-300 kcmil
AAAC 5005 Run (Range)	N/A
Approvals / Certifications	
ROHS Compatible	Compliant
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175