



PATCUT129ACSR18V

Catalog ID: PATCUT129ACSR18V

Prop 65 Notice

Battery Actuated Cutting Tool, Hydraulic Self Contained, 1.29" Copper(Max), 1.29" Aluminium(Max), 1113 ACSR(Max),18V Ni-MH, 5/8" Ground Rod.

- Special Latch head design provides interference free closure for Mid-Span cuts
- 180° head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold
- Durable high impact carrying case

Features: Battery powered cutting technology, easy tool operation and portability, Advance design high-speed pump completes tough cuts faster Longer life, efficiency, and reliability, Specialized latch head design, interference free closure for mid-span cuts, Ergonomic design allows one hand operation User has one hand free to manipulate material to be cut, 180 degree head rotation, versatile head positioning allows user to get into tight areas easier, Mechanical ram release reliable ram release (no battery power consumption), Operates on 18 volt Ni-MH batteries eliminates voltage depression or memory issues, Durable high impact formed carrying case provides tool protection and stores all accessories, 5-year limited warranty on tool (excluding blades), 1 year on batteries and charger5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Application	For Use On: Copper Cable: up to 1.29 IN, Aluminum Cable: up to 1.29 IN, ACSR: up to 1113 ACSR, Ground Rod: up to 5/8 IN, Rebar: up to 1/2 IN, Soft Steel Bolts: up to 5/8 IN, Standard Guy Strand: up to 1/2 IN, EHS Guy Strand: up to 3/8 IN
Battery Type	2.6 Ah Ni-MH
Crimp Force Capacity	7 ton
Die Type	Dieless
Recharge Time	0.75 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutting Tool
Trade Name	PATRIOT®
Туре	Cutters
UPC	781810370803
UPC 12 Digit	7818103708033

Dimensions

Height	12.80 in
Length	14.5 in
Weight	12.0 lb
Width	3.7 in

Electrical Ratings

Certifications and Compliance					
Certification - CSA Approved	No				
Certification - ETL	No				
Certification - UL Recognized	No				
Certification - cULus	No				
Standards - RoHS Compliance Status	EX				
UL Listed	No				

18 V-DC V

Logistics

Operating Voltage

Minimum Pack Quantity	1	

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)