



CL501

by Burndy
Catalog ID: CL501

Prop 65 Notice

Copper Lay-in Lug, 14-4 AWG, #10 Stud.

Features: The Lay-In QIKLUG Is Manufactured From High Strength Pure Electrolytic Copper To Ensure Maximum Strength And Conductivity, UL467 Listed For Direct Burial In Earth Or Concrete, The Open-Faced Design Allows For Fast Lay-In Of The Conductor Without The Need For Cutting Or Breaking, Stud/bolt Size: #10, Stud/bolt Hole Size: 0.22 IN, Installation Torque: Yes, Set Screw Type: Slot, Length: 1.13 IN, Height: 0.85 IN, Tongue Width : 0.38 IN

Product Details

General

Application	For Direct Burial Applications In Concrete Or Earth, For Fast Lay-In Of The Conductor Without The Need For Cutting Or Breaking
Material	Copper
Material - Hardware	Stainless Steel
Plated	N
Plating Type	Unplated
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	Open-Faced
UPC	781810276150
UPC 12 Digit	7818102761500

Dimensions

Dimension - D inch	0.47 in
Dimension - Height inch	0.85 in
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.13 in
Dimension - N inch	0.19 in
Dimension - Stud Size inch	17/64
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG

Conductor Type	CU C Str-Size
----------------	---------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)