



## BIBS3506DB

by Burndy  
Catalog ID: BIBS3506DB

Prop 65 Notice

Direct Burial Unitap, 350 Kcmil -12 AWG Str., 7.45 in L, Designed specifically for direct burial applications.

Dual rated for aluminum or copper conductors, Each unit is individually marked for ease of identification

## Product Details

### General

Application	For Outside Direct Burial
Installation Torque Recommended in-lb	450 LBS/in
Insulation	Y
Material	Aluminum
Number Of Ports	6
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523629
UPC 12 Digit	7818105236299

### Dimensions

Dimension - Height inch	2.46 in
Dimension - L Length Overall mm	189 mm
Dimension - Length Overall inch	7.45 in
Dimension - Strip Length inch	1.125
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size Range	12 - 350 Str
Conductor - Copper Str Size Range	12 - 350 Str
Conductor Type	<ul style="list-style-type: none"> <li>AL C Str-Size</li> <li>CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)