



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	<ul style="list-style-type: none"> Baying hardware Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels
--------------------	--

Physical

Maximum Mounting Depth	41.26 in (104.8 cm)
Number of rack unit	45U
Minimum Mounting Depth	7.52 in (19.1 cm)
Marking	<ul style="list-style-type: none"> 14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Color	Black
Maximum Depth	47.24 in (120 cm)
Rack Width	19"
Height	83.62 in (212.4 cm)
Net Weight	310.85 lb(US) (141 kg)
Permanent permissible load	<ul style="list-style-type: none"> 1020.58 Kg dynamic 3750 lb(US) (1700.97 kg) static
Width	23.62 in (60 cm)

Conformance

Standards	<ul style="list-style-type: none"> UL 2416 UL 60950-1 EIA-310E
-----------	---

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304290216
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	TH

Packing Units

Package 1 Height	88.19 in (224 cm)
Package 1 width	29.37 in (74.6 cm)
Package 1 Length	52.52 in (133.4 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------