

# AR3100

## APC NetShelter SX 42U Server Rack Enclosure 600mm x 1070mm w/ Sides Black



### Overview

Presentation	Standard enclosure for low to medium density server and networking applications. Compact width to optimize data center space. 42U height to easily roll through doorways.
Lead time	Usually in Stock

### General

Provided equipment	Baying hardware Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels
--------------------	--

### Physical

Maximum Mounting Depth	36.02 in (91.49 cm)
Number of rack unit	42U
Minimum Mounting Depth	7.52 in (19.1 cm)
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Color	Black
Maximum Depth	42.13 in (107 cm)
Rack Width	19"
Height	78.39 in (199.1 cm)
Net Weight	275.78 lb(US) (125.09 kg)
Permanent permissible load	1020.58 Kg dynamic 3750 lb(US) (1700.97 kg) static
Width	23.62 in (60 cm)

### Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304226390
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

## Packing Units

Package 1 Height	83.39 in (211.8 cm)
Package 1 width	29.61 in (75.2 cm)
Package 1 Length	45.51 in (115.6 cm)
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------