



**JC TYPE LAMPS** are low voltage capsules with pin bases.



Order code	Description	Watts (W)	Base	Volts (V)	Colour/Finish	Average life (hrs)	Initial lumens (lm)	Case qty
<b>JC (G4)</b>								
MOL : 1 7/16 in. (33 mm) Dia. : 11/32 in. (9 mm)								
51129	H10JC/CL/2M/G4/12V/STD	10	G4	12	Clear	2 000	130	100
51130	H20JC/CL/2M/G4/12V/STD	20	G4	12	Clear	2 000	300	100
<b>JC (GY6.35)</b>								
MOL : 1 29/32 in. (44 mm) Dia. : 15/32 in. (12 mm)								
50902	H50JC/CL/4M/GY6.35/12V/STD	50	GY6.35	12	Clear	4 000	900	100
<b>JC (GY6.35)</b>								
MOL : 2 1/4 in. (57 mm) Dia. : 15/32 in. (12 mm)								
22121	200T4/CL/32V/GY9.5/STD 1945	200	GY9.5	32	Clear	200	4 500	100

**JD TYPE LAMPS** are tubular shaped and run on line voltage. JD halogen lamps can have E26, BA15d, E11, E12, E14 and G9 bases.



Order code	Description	Watts (W)	Base	Volts (V)	Colour/Finish	Average life (hrs)	Initial lumens (lm)	Case qty
<b>T3 (BA15d)</b>								
MOL : 2 7/32 in. (56 mm) Dia. : 19/32 in. (15 mm)								
50881	H75T3/CL/2M/BA15D/130V/STD	75	BA15d	130	Clear	2 000	1 120	120
50950	H100T3/CL/2M/BA15D/130V/STD	100	BA15d	130	Clear	2 000	1 600	50
50883	H150T3/CL/2M/BA15D/130V/STD	150	BA15d	130	Clear	2 000	3 000	120
50885	H250T3/CL/2M/BA15D/130V/STD	250	BA15d	130	Clear	2 000	4 800	50
<b>T3 (E11)</b>								
MOL : 2 15/32 in. (63 mm) Dia. : 23/32 in. (18 mm)								
55028	H50T3/CL/2M/E11/130V/STD	50	E11	130	Clear	2 000	1 120	120
50880	H75T3/CL/2M/E11/130V/STD	75	E11	130	Clear	2 000	1 350	120
50882	H100T3/CL/2M/E11/130V/STD	100	E11	130	Clear	2 000	1 800	120
50951	H150T3/CL/2M/E11/130V/STD	150	E11	130	Clear	2 000	3 000	120
50884	H250T3/CL/2M/E11/130V/STD	250	E11	130	Clear	2 000	4 800	50



# JC & JD Lamps