

Actual

Catalog Number: RCC26

 Product ID:
 7TAI029860R0070

 UPC Number:
 78621081970

 EAN Number:
 05414363159575

Status: Active

Nylon Insulated Parallel Splice, Length .90 Inches, Width .28 Inches, Wire Range #14-#12 AWG, Color Yellow, Copper, Tin Plated, 500 Pack

- Wires are laid side by side in the connector, and the splice connection is complete in one crimp.
- Application Tools: WT2000, WT112M
- Alternate Package Qty: 2C12

<b>North American Specif</b>	ications (UNSPSC)	
UNSPSC	39121449 Wire or cable compression splice	
IGCC	4669 Wire or cable compression splice	
Brand Name	Sta-Kon	
Туре	Splice Connector	
Special Features	Wires are laid side by side in the connector, and the	
	splice connection is complete in one crimp.	
Standard	UL E9809	
Material	Copper	
Finish	Tin Plated	
Color	Yellow	
Voltage Rating	600V	
Temperature Rating	105 Degrees C	

<b>European Specifications (ETIM</b>	1)
ETIM	EC001059 Crimp splices for copper conductor
AWG-range	14-12
Material	Copper
Surface protection	Tinned
Insulation	PA
Colour insulation	Yellow

Packaging	
Inner Quantity	500
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	5000
Outer Dimensions (inches)	12.3x10.2x8.2
Weight Uom	3.13 lbs. per 1000

<b>Documents / Support Tools</b>		
Technical Drawing / Data Sheet US	Available on Website	
Technical Drawing / Data Sheet Canada	Available on Website	

## For further technical assistance, please contact us...

ABB Installation Products Technical Support MS 3B-50

860 Ridge Lake Blvd. Memphis, TN 38120 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

ABB Installation Products - USA 860 Ridge Lake Blvd. Memphis, TN 38120 www.tnb.com