



Representative Image

**Alternate Catalog No. XT6NU3800BFF000XXX**  
**Catalog No. 1SDA102839R1**

**Description:** XT6N 800 TMA IN800A 3P F F UL

**UPC No** 8015644033507

**Home > Circuit Breakers > Molded Case Circuit Breakers > SACE Tmax XT**

C.BREAKER TMAX T6N 800 UL/CSA FIXED THREE-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMA R 800 I3=4000...8000 A A FULLY RATED NEUTRAL

## Descriptors

|          |              |
|----------|--------------|
| Category | SACE Tmax XT |
|----------|--------------|

## Specifications

|                       |                                |
|-----------------------|--------------------------------|
| Trip Unit             | TMA                            |
| Product Main Type     | SACE Tmax XT                   |
| Frame size            | XT6                            |
| Extended Product Type | XT6N 800 TMA In=800A 3p F F UL |
| Standards             | UL                             |
| Rated Current         | 800 A                          |
| Interruption Rating   | N (35kA @480VAC)               |
| Number of Poles       | 3                              |

## Approvals

|               |    |
|---------------|----|
| Certification | UL |
|---------------|----|