



#### M12™ Palm Nailer Kit

2458-21 (2458-20 Tool-Only)

# **Specifications:**

Impact Energy	2.2 ft-lbs (3.0 J)
BPM	0 – 2,700
Collet Capacity	6D – 16D
Head Profile	3/4"
Magnetic Tip	Yes
Weight	3.4 lbs

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, Hand Strap, Charger, Soft Carrying Case



# M12™ 23 Gauge Pin Nailer Kit

2540-21 (2540-20 Tool-Only)

#### Specifications:

Nail Diameter	23 Gauge
Nail Size	1/2" - 1-3/8"
Magazine Capacity	120 Nails
Magazine Loading	Side Load
Firing Modes	Sequential
Length / Weight	8.7" / 3.8 lbs

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, Reversible Belt Clip, Jam Clearing Guide, Hex Wrench, Secondary Tip, Charger, Contractor Bag



# M12<sup>™</sup> 3/8" Crown Stapler Kit

2447-21 (2447-20 Tool-Only)

#### **Specifications:**

Staple Crown Size	3/8" Flat Crown
Staple Length	1/4" - 9/16"
Staple Type	T-50
Length / Weight	7.3" / 3.0 lbs

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, Charger, Contractor Bag



### 

# 1/4" Right Angle Die Grinder Kit

2485-22 (2485-20 Tool-Only)

#### **Specifications:**

Power Output	0.3 HP
RPM	0 – 24,500
Collet Size	1/4"
Accessory Size	2"
Height / Length	8.7" / 4.5"
Weight	1.7 lbs

**Includes:** (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Packs,

Related Accessories:

**49-16-2485** M12 FUEL" 1/4" Right Angle Die Grinder Rubber Boot **48-07-2486** 1/4" Cut-Off Wheel Arbor

48-66-2486 1/8" Collet & Nut Kit

49-94-2000 2" Metal Cut-Off Wheel



## 

# 1/4" Straight Die Grinder Kit

2486-22 (2486-20 Tool-Only)


## **Specifications:**

Power Output	0.3 HP
RPM	0 - 21,000
Collet Size	1/4"
Accessory Size	2"
Height / Length	2" / 11"
Weight	1.6 lbs

**Includes:** (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Packs, (2) Wrenches, Charger, Carrying Case

**Related Accessories:** 48-07-2486 1/4" Cut-Off Wheel Arbor

48-66-2486 1/8" Collet & Nut Kit 49-94-2000 2" Metal Cut-Off Wheel





2466-22 (2466-20 Tool-Only)

#### **Specifications:**

Torque Range	12.5 - 150 ft-lbs
RPM	0 – 100
Tool Accuracy	CW: +/-2% of Full Scale / CCW: +/-3% of Full Scale (Range: 20% – 100% of Full Scale)
Ratcheting Angle	4.5°
Anvil Size	1/2" Ball Detent
Measuring Units	ft-lbs, in-lbs, Nm, kg-cm
Length / Weight	23.5" / 5.7 lbs

**Includes:** (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Packs, Certificate of Calibration, Charger, Carrying Case




# 3/8" Digital Torque Wrench w/ ONE-KEY™ Kit

2465-22 (2465-20 Tool-Only)

**Specifications:** 

Torque Range	10 - 100 ft-lbs
RPM	0 – 100
Tool Accuracy	CW: +/-2% of Full Scale / CCW: +/-3% of Full Scale (Range: 20% – 100% of Full Scale)
Ratcheting Angle	4.5°
Anvil Size	3/8" Ball Detent
Measuring Units	ft-lbs, in-lbs, Nm, kg-cm
Length / Weight	23.3" / 5.5 lbs

**Includes:** (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Packs, Certificate of Calibration, Charger, Carrying Case





# M12™ Spot Polisher Kit

2438-22X, 2438-22 (2438-20 Tool-Only)

# Specifications:

Polishing RPM	0 – 2,800
Sanding RPM	0 - 8,300
Length / Weight	5.1" / 2.4 lbs

Includes: 2438-22X (1) M12™ REDLITHIUM™ XC3.0 Battery Pack, (1) M12™ REDLITHIUM™ CP1.5 Battery Pack; 2438-22 (2) M12™ REDLITHIUM™ CP1.5 Battery Packs; All Kits Include: 5 Pc Accessory Pack, Side Handle, Charger, Soft Carrying Case

# 

# **Low Speed Tire Buffer Kit**

2409-22 (2409-20 Tool-Only)

# Specifications:

DRIVE CONTROL™	2-Mode
Collet	7/16" Quick Change
RPM (Buffing)	0 – 2,500
RPM (Drilling)	0 – 1,200
Lenath / Weight	10.1" / 1.8 lbs

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack, (1) M12<sup>™</sup> REDLITHIUM™ CP2.0 Battery, Quick Change Adapter, Charger, Carrying Case **Related Accessories:** 

**49-93-2410** 2" Flared Contour Buffing Wheel **49-93-2409** 2-1/2" Flared Contour Buffing Wheel



# M12 FUEL 5-3/8" Circular Saw Kit

2530-21XC (2530-20 Tool-Only) Specifications:

-		and the second
RPM	3,600	17.
Bevel Capacity	50°	1
Cut Capacity	1-5/8" at 90°; 1-1/8	' at 45°
Arbor	10 mm	
Blade Guards	Aluminum	
Weight	6.2 lbs	

Includes: (1) M12™ REDLITHIUM™ XC4.0 Battery Pack, Circular Saw Blade, Wrench, Charger, Contractor Bag



M12 FUEL HACKZALL® One-Handed **Reciprocating Saw Kit** 

2520-21XC (2520-20 Tool-Only) Specifications:

SPM 0 - 3,000Stroke Length 5/8" QUIK-LOK<sup>11</sup> Keyless (Accepts all SAWZALL® Blades) Blade Clamp Length / Weight 13.3" / 4.1 lbs

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack. Charger, Contractor Bag

M12™ HACKZALL® One-Handed **Reciprocating Saw Kit** 

2420-22, 2420-21 (2420-20 Tool-Only)

#### Specifications:

SPM	0 – 3,000
Stroke Length	1/2"
Keyless Blade Clamp	QUIK-LOK™ (Accepts all SAWZALL® Blades)
Length / Weight	11.0" / 2.6 lbs

**Includes: 2420-22** (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Packs; **2420-21** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack; All Kits Include: Charger, Contractor Bag

# M12™ High Performance Jig Saw Kit

2445-21 (2445-20 Tool-Only)

# **Specifications:**

•	
SPM	0 – 2,800
Stroke Length	3/4"
Bevel Capacity	45° (Positive Locks at 90° and 45°)
Blade Clamp	QUIK-LOK™ T-Shank
Length / Weight	8.8" / 4.2 lbs

**Includes:** (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Anti-Splintering Insert, Non-Marring Shoe, Charger, Contractor Bag

## M12 FLEL **Oscillating Multi-Tool Kit**

2526-21XC (2526-20 Tool-Only)

#### Specifications: 12 Speed Settings OPM 10,000 - 20,000 Oscillation Angle 3.9° Tool-Free Accessory Change Yes

Length / Weight 13" / 3.2 lbs **Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack, (5) Sanding Sheets, (1) Sanding Pad, (1) Wood Cutting Blade, Charger, Contractor Bag

Yes

## M12™ Oscillating Multi-Tool Kit

2426-22, 2426-21 (2426-20 Tool-Only)

LED Light

Specifications:	- 1
Speed Settings	12
OPM	5,000 – 20,000
Lenath / Weiaht	10.9" / 2.1 lbs

**Includes: 2426-22** (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Packs; **2426-21** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack; All Kits Include: Wood Cutting Blade, Sanding Pad, (5) Assorted Sanding Sheets, Charger, Contractor Bag

# M12 FUEL HATCHET™ 6" Pruning Saw Kit

2527-21 (2527-20 Tool-Only)

#### Specifications:

Bar Length	6"
Chain Gauge	.043"
Chain Pitch	3/8" Low Profile
Chain Speed	5 m/s
Oiler	Automatic
Trigger	Variable Speed
Length / Weight	18.3" / 4.8 lbs

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack, 6" Oregon® Bar & Chain, Scrench, Scabbard, Charger Related Accessories:

49-16-2732 6" Saw Chain 49-16-2733 6" Guide Bar



# **Compact Band Saw Kit**

2529-21XC (2529-20 Tool-Only)

## Specifications:

	SFPM	0 – 570
	Blade Size	30-9/16"
	Cut Capacity	2-1/2" x 2-1/2"
	LED Light	Yes
	Hang Hook	Yes
	Reamer Attachment Compatibility	Yes

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack, 12/14 TPI Compact Extreme Thin Metal Band Saw Blade, Charger, Contractor Bag Related Accessories:

**49-90-2029** Compact Band Saw Reamer Attachment **48-39-0630** 30-9/16" 8/10 TPI Compact Extreme Thick Metal Band Saw Blade 3 pk

48-39-0631 30-9/16" 12/14 TPI Compact Extreme Thick Metal Band Saw Blade 3 pk **48-39-0635** 30-9/16" 8/10 TPI Compact Extreme Thick Metal Band Saw Blade 25 pk

48-39-0636 30-9/16" 12/14 TPI Compact Extreme Thick Metal Band Saw Blade 25 pk

**48-39-0637** 30-9/16" 8/10 TPI Compact Extreme Thick Metal Band Saw Blade 100 bulk 48-39-0639 30-9/16" 12/14 TPI

Compact Extreme Thick Metal Band Saw Blade 100 bulk





2429-21XC (2429-20 Tool-Only)

#### **Specifications:**

-	
SFPM	280
Blade Size	27"
Cut Capacity	1-5/8" x 1-5/8"
Length / Weight	11.0" / 6.7 lbs

**Meets OSHA Guarding** Requirements. Suitable for One-Handed Use.

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC3.0 Battery Pack, 18 TPI Sub-Compact Portable Band Saw Blade, Charger, Carrying Case **Related Accessories:** 

48-39-0572 18 TPI Sub-Compact Portable Band Saw Blades (3 pk) 48-39-0711 12/14 TPI Extreme Metal Sub-Compact Portable Band Saw Blades (3 pk)

# 

3" Compact Cut-Off Tool Kit 2522-21XC (2522-20 Tool-Only)

## Specifications:

Blade Size	3"
RPM	20,000
Arbor Size	3/8"
Cut Depth	0.64"
Blade Rotation	Reversible
Length / Weight	8.9" / 2.4 lbs

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> XC4.0 Battery Pack, Dust Accessory Shoe, (3) Accessory Blades (Metal Cut-Off, Carbide Abrasive, Diamond Tile), Blade Wrench, Charger, Contractor Bag

# M12™ Rotary Tool Kit

2460-21 (2460-20 Tool-Only)

# **Specifications:**

Speed Settings	6
RPM	5,000 - 32,000
Collet	1/8", Universal
Length / Weight	9.5" / 1.3 lbs

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, (5) Cutting Wheels, Mandrel, Wrench, Charger, Soft Carrying Case **Related Accessory:** 49-94-1500 5 Pc Reinforced Cut-Off Wheels

#### M12™ 10 oz Caulk & **Adhesive Gun Kit**

2441-21 (2441-20 Tool-Only)

# **Specifications:**

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	4.1 lbs

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, 10 oz Carriage, M12™ 10 oz Plunger Rod and Piston Assembly, Charger

# M12™ 20 oz Aluminum Barrel Sausage **Style Caulk & Adhesive Gun Kit**

2442-21

	The second second	
Specifications:	-	
Force	400 lbs	
Inches Per Minute	0 – 29	
Speed Settings	6	
Auto-Reverse Anti-Drip	Yes	
Weight	4 9 lhs	

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, 20 oz Aluminum Sausage Style Barrel, M12™ 20 oz Plunger Rod and Piston Assembly, Nozzle, Charger

#### M12™ Quart Caulk & **Adhesive Gun Kit**

2444-21

#### Specifications:

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	5.5 lbs
	Inches Per Minute Speed Settings Auto-Reverse Anti-Drip

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Quart Carriage, M12™ Quart Plunger Rod and Piston Assembly, Charger

#### **Caulk Gun Accessories**

Compatible with 2441-21, 2442-21, 2444-21

31-12-0700 Caulk Gun Nozzle - Black

48-08-0900 M12™ 10 oz Caulk and Adhesive Gun Conversion Kit

**48-08-0905** M12<sup>™</sup> 20 oz Aluminum Barrel Sausage Style Caulk and Adhesive Gun Conversion Kit

**48-08-0910** M12<sup>™</sup> Quart Caulk and Adhesive Gun Conversion Kit

48-08-1091 20 oz Aluminum Barrel Kit

48-08-1096 20 oz Clear Barrel Kit

# M12™ Grease Gun Kit

2446-21XC (2446-20 Tool-Only)

# Specifications:

	Output Pressure	Over 8,000 PSI	
	Run-Time	Up to 7 Grease Cartridges Per Charge	е
	Grease Capacity	14 oz Cartridge, 16 oz Bulk, 16 oz Suction	
	Air Bleeder Valve	Yes	

7.2 lbs

Includes: (1) M12™ REDLITHIUM™ XC3.0 Battery Pack. 36" Flex Hose with Spring Guard, Grease Coupler, Charger, Carrying Case

# M12™ Soldering Iron Kit

2488-21 (2488-20 Tool-Only)

#### Specifications:

Weight

0°F
Watts
Seconds
S
isel and Point
.6" / 0.9 lbs

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, Chisel Tip, Pointed Tip, Charger, Carrying Case

# M12™ Cable Stapler Kit

2448-21 (2448-20 Tool-Only)

# Specifications:

Firing Mode	Sequential
Magazine Capacity	45
Magazine Loading	Front Load
Run-Time	1,200 Staplers per Charge on M12™ CP2.0 Battery
Length / Weight	6.5" / 5.0 lbs

Includes: (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Charger, Carrying Case
Related Accessory:



# M12™ Cable Stripper Kit


2435CU-21S, 2435AL-21, 2435X-21 (2435-20 Tool-Only)

# Specifications:

Yes
Yes
Industry Standard Quick-Change
8.6" x 2.8" x 11.5"
3.6 lbs

Includes: 2435CU-21S 1/0 AWG - 750 MCM Cu THHN / XHHW Bushings; **2435AL-21** 1/0 AWG - 750 MCM AI THHN / XHHW Bushings; **2435X-21** 1/0 AWG – 500 MCM Cu RHW / RHH / USE Bushings; **All Kits Include:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP2.0 Battery Pack, Multi-Voltage Charger, Carrying Case

#### Reference Available Bushings on Pg. 66



## M12™600 MCM Cable Cutter Kit

2472-21XC (2472-20 Tool-Only)

#### Specifications:

Specifications.		
Cut Capacity	600 MCM Copper, 750 MCM Aluminum, 1-3/16" Communication Cable	
Jaw Opening	1-7/16"	
Two-Speed	Yes	
Length / Weight	10.5" / 6.7 lbs	

Includes: (1) M12™ REDLITHIUM™ XC3.0 Battery Pack, Charger, Carrying Case
Related Accessory:
48-44-0410 M12™ 600 MCM Cable Cutter Blade

#### M12™ Plastic Pipe **Shear Kit**

2470-21 (2470-20 Tool-Only)

# **Specifications:**

Cut Capacity	Up to 2" Schedule 80 PVC
Torque	1,900 in-lbs
Blade	3 mm Reinforced Stainless Steel
Length / Weight	14.4" / 4.4 lbs

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack,

Related Accessory: Pipe Shear Blade

## M12™ Copper Tubing **Cutter Kit**

2471-22, 2471-21 (2471-20 Tool-Only)


#### Specifications:

specifications.		
Cut Capacity	3/8" - 1" (1/2" - 1-1/8" O.D.)	
Tubing Type	M, L and K Copper	
RPM	500	
Length / Weight	14.0" / 3.2 lbs	

**Includes: 2471-22** (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Packs; **2471-21** (1) M12™ REDLITHIUM™ CP1.5 Battery Pack;

All Kits Include: Charger, Carrying Case

Related Accessory: 48-38-0010 Copper Cutter Wheel (2 pk)



# M12 FLEL ProPEX® Expander Kit w/ 1/2" - 1" RAPID SEAL **ProPEX® Expander Heads**

2532-22 (2532-20 Tool-Only)

#### **Specifications:**

3/8" - 1"
Built-In
Dual Actuating
7.1" x 3.7" x 12.8"
4.5 lbs

Includes: (3) ProPEX® Expander Heads w/ RAPID SEAL™ (1/2", 3/4", 1"), ProPEX® Expander Cone Grease, Carrying Case; 2532-22 (2) M12™ REDLITHIUM™ CP2.0 Battery Packs, Charger

Helated	Accessories:
49-16-2414	1/2" ProPEX® Expander Head w/ RAPID SEAL®
49-16-2415	5/8" ProPEX® Expander Head w/ RAPID SEAL"
49-16-2416	3/4" ProPEX® Expander Head w/ RAPID SEAL"
49-16-2418	1" ProPEX® Expander Head w/ RAPID SEAL™

#### M12™ ProPEX® Expansion Tool Kit

2432-22 (2432-20 Tool-Only)

## Specifications:

Capacity	3/8" - 1"
Auto-Rotate	Built-In
Head Compatibility	3/8" - 1" M12™ / Uponor
Dimensions (L x W x H)	7.1" x 3.7" x 12.8"
Weight	5.0 lbs

Includes: (3) ProPEX® Expansion Heads (1/2", 3/4", 1"), ProPEX® Tool Cone Grease, Carrying Case; 2432-22 (2) M12™ REDLITHIUM™ CP1.5 Battery Packs, Charger

## Related Accessories:

49-08-2400 ProPEX® Expander Cone Grease 49-16-2403 3/8" ProPEX® Expansion Head 49-16-2404 1/2" ProPEX® Expansion Head 49-16-2405 5/8" ProPEX® Expansion Head 49-16-2406 3/4" ProPEX® Expansion Head 49-16-2408 1" ProPEX® Expansion Head

# M12™ PEX Expansion Tool Kit

2474-22

# **Specifications:**

-	
Capacity	3/8" - 1"
Auto-Rotate	Built-In
Head Compatibility	3/8" - 1" M12™
Dimensions (L x W x H)	7.1" x 3.7" x 12.8"
Weight	5.0 lbs

**Includes:** (2) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Packs, (3) PEX Expansion Heads (1/2", 3/4", 1"), PEX Tool Cone Grease, Charger, Carrying Case

# Related Accessories:

49-16-2424 1/2" PEX Expander Head 49-16-2426 3/4" PEX Expander Head 49-16-2428 1" PEX Expander Head 49-08-2402 PEX Tool Grease



# M12™ TRAPSNAKE™ 6¹ Toilet Auger Kit

2576-21 (2576-20 Tool-Only)

#### **Specifications:**

RPM	0 – 500
Cable Lock	Yes
Cable Size	6' x 1/2"
Cable Head	Retriever Bulb
Replacement Cables	Available
Weight	9.0 lbs

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Cable, Charger **Related Accessories:** 

48-53-2576 TRAPSNAKE™ 6' Toilet Auger Replacement Cable 48-22-2576 TRAPSNAKE™ Toilet Auger Case

# M12™ TRAPSNAKE™ 4¹ Urinal Auger Kit

2574-21 (2574-20 Tool-Only)

#### **Specifications:**

RPM	0 – 500
Cable Lock	Yes
Cable Size	4' x 3/8"
Cable Head	Bulb
Replacement Cables	Available
\Mojaht	6.4 lbc

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Cable, Charger Related Accessories:

48-53-2577 TRAPSNAKE™ 4' Urinal Auger Replacement Cable 48-22-2577 TRAPSNAKE™ Urinal Auger Case




# M12™ Pipeline Locator Kit

### 2580-21

#### Specifications:

•	
Sonde Frequencies	512Hz, 640Hz, 8,192kHz, 33kHz, 83kHz
Line Trace	33kHz, 83kHz
Power Frequency	50Hx, 60Hz
Radio Frequency	10kHz – 22.7kHz Bandwidth
Display Type	4.3" Color LCD Display
Water & Dust Rating	IP65

Includes: (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack. Charger, Carrying Case



#### M12™ Drain Snake Kit 2571-21 (2571-20 Tool-Only)

#### Specifications:

ppoomod monor	
Max Drain Line Capacity	1-1/4" – 2-1/2", Up to 25'
Drum Capacity	1/4" x 25', Best for 1-1/4" – 2" drain lines; 5/16" x 25', Best for 1-1/4" – 2-1/2" drain lines
Variable Speed Spin	0 – 500 RPM
LED Light	Yes
Weight (without cable)	6.5 lbs

**Includes:** (1) M12<sup>™</sup> REDLITHIUM<sup>™</sup> CP1.5 Battery Pack, 5/16" x 25' Inner Core Bulb Head Cable with Inner Drum, Charger, 5 Gallon Storage Bucket

#### **Related Accessories:**

48-53-2561 5/16" x 25' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating

48-53-2562 5/16" x 25' Inner Core Drop Head Cable w/ RUST GUARD™ Plating 48-53-2563 1/4" x 25' Inner Core Bulb Head Cable

w/ RUST GUARD™ Plating

48-53-2564 1/4" x 25' Inner Core Drop Head Cable w/ RUST GUARD™ Plating

# M12™ TRAPSNAKE™ **Driver Upgrade Kit**

2575-21

# **Specifications:**

500
11"
4.5 lbs

Includes: (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, Charger

**Related Accessories:** 49-16-2576 TRAPSNAKE™ 6' Toilet Auger 49-16-2574 TRAPSNAKE™ 4' Urinal Auger

49-16-2573 TRAPSNAKE™ 25' Auger w/ CABLE DRIVE™



# M12™ AIRSNAKE™ **Drain Cleaning Air Gun Kit**

2572B-21, (2572B-20 Tool-Only) **Specifications:** 

# Max Drain Line Capacity



Includes: 2572B-21 (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Charge

All Kits Include: 2572B-20: 1" - 2" Drain Plug, - 3" Drain Plug, 3" - 4" Drain Plug, Drain Shroud Attachment, Toilet Seal Attachment, 10" Extension, (3) Straight Connectors, 15° Offset Connector, Carrying Case