



GENERAL SPECIFICATIONS

ITEM NUMBER:	S11279
WATTAGE:	10W
VOLTAGE:	120V
FINISH:	White
COLOR TEMPERATURE:	2700K-5000K

-  RGB Bulb, millions of colors
-  Tunable White, 90 CRI, 2700K - 5000K
-  Yes-Dimmable
-  Wet Location
-  IC Rated
-  Air Tight Rated

COMPLIANCE

SAFETY LISTING:



TECHNICAL SPECIFICATIONS

TECHNOLOGY:	LED
WATTAGE:	10W
LUMEN OUTPUT:	650L
COLOR TEMPERATURE:	2700K-5000K
CRI:	90
VOLTAGE:	120V
POWER FACTOR:	0.9
BEAM ANGLE:	110
RATED HOURS:	25000
OPERATING TEMPERATURE:	-20C (-4F) to a maximum of +45C (+113F)
DIMMABLE:	Yes-Dimmable
DIMMING FUNCTION:	Only with Starfish App; Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
IC RATED:	Yes

DIMENSIONS

HEIGHT	1.50
--------	------

PACKAGING

EACH QTY	1
EACH UPC	045923112799
EACH DIMENSIONS	5.51 x 3.15 x 5.51
INNER QTY	0
INNER UPC	
INNER DIMENSIONS	0.00 x 0.00 x 0.00
CASE QTY	6
CASE UPC	10045923112796
CASE DIMENSIONS	11.81 x 10.04 x 6.10

SATCO DISTRIBUTION CENTERS

NEW YORK (HQ)	TEXAS	FLORIDA	CALIFORNIA	WASHINGTON	PUERTO RICO
110 HEARTLAND BLVD BRENTWOOD, NY 11717 T. 631-243-2022 F.631-243-2027	2000 VALWOOD PKWY FARMERS BRANCH, TX 75234 T. 972-247-2437 F.972-247-5408	900 NW 159TH DR MIAMI, FL 33169 T. 305-624-2044 F.305-623-0286	31288 SAN BENITO ST HAYWARD, CA T. 510-487-4822 F.510-487-8955	4710 116TH ST SW MUKILTEO, WA 98275 T. 425-789-3300 F.425-789-3310	CAMPECHE STREET, 23 JULIO N. MATOS INDUSTRIAL PARK T. 787-757-3510 F.787-757-3540

PRODUCTS INVENTORIED IN CANADA & MEXICO: INTERNATIONALSALES@SATCO.COM/631 -243-2022 EXT. 315