

# APC Back-UPS<sup>®</sup> Pro 700

## Power-Saving, high performance power protection for office computers

The Back-UPS Pro provides abundant battery backup power, so you can work through medium length power outages. It safeguards your equipment against damaging surges and spikes that travel along utility and data lines. The Back-UPS Pro also features automatic voltage regulation (AVR), which instantly adjusts high and low voltages to safe levels, so you can work indefinitely during brownouts and overvoltages.

The Back-UPS Pro also includes unique “green” features, like power-saving outlets that automatically turn off idle peripherals. A high efficiency charging system and “AVR Bypass” also reduce power consumption. With the rest of the Back-UPS Pro’s standard features, this is the perfect unit to protect your productivity from the constant threat of bad power and lost data.

## Product Features:



**1 LCD (Liquid Crystal Display)** gives the status of over 20 different utility and battery backup conditions.

**2 Automatic Voltage Regulation (AVR)** instantly corrects voltage fluctuations so you can work indefinitely through brownouts and overvoltages.

**3 “Battery Backup & Surge Protected” Outlets** keep a CPU, monitor and other critical devices running when the power goes out or fluctuates outside safe levels.

**4 3 “Surge Only” Outlets** protect printers, faxes or other equipment without reducing battery capacity. (Includes two power-saving “Controlled” outlets).

**5 Data Line Surge Protection** guards against surges and spikes traveling over Ethernet or coax cable lines.

**6 PowerChute Software** lets you use your computer to access additional power protection and management features:

- Preserves your work, shuts down system during outages
- Restarts your system, minimizing work disruptions
- Enables customization of your Back-UPS settings
- Monitors and displays power and battery status

**7 Push Button Circuit Breaker** enables quick recovery from overloads.

**8 3 Yr Warranty, \$150,000 Equipment Protection Policy, free technical support and data recovery services.**

**9 Automatic Diagnostic Testing** ensures your unit is ready when you need it.



**APC**  
by Schneider Electric

## Back-UPS Pro 700 Specifications

Model Number	BR700G
<b>Output</b>	
Output Capacity	700 VA / 420 Watts
Output Volt. / Freq. (on utility)	120V, 50 or 60 Hz, +/- 3Hz (auto sensing)
Output Volt. / Freq. (on battery)	115V +/-8%, 50 or 60Hz +/-1Hz (auto sensing)
Output Connections	6 total NEMA 5-15R outlets: 3 battery & surge 3 surge protection only (incl. 2 <i>Controlled</i> outlets)
Waveform Type	Stepped Approximation to Sine Wave
<b>Input</b>	
Input Voltage, Frequency	120V, 50 or 60 Hz, +/- 3Hz
Input Connection	6 ft cord with NEMA 5-15 plug
<b>Surge Protection</b>	
AC Power Surge Protection	All outlets
Data Line Surge Protection	Network: 10/100/1000 Base-T Ethernet (gigabit) Coax cable (CATV, SATV, modem, A/V)
<b>Physical</b>	
Unit Dimensions (H x W x D)	7.5 x 3.6 x 12.2"
Unit Weight	15.7 lbs
Shipping Dims. (H x W x D)	5.43" x 9.92" x 17.40"
Shipping Weight	17.5 lbs
Color	Black
UPC Code	731304266792
<b>Battery</b>	
Battery Type	Sealed, lead-acid, maintenance-free
Extended run battery pack compatibility	No
<b>Management</b>	
Alarms	Visual (LCD) and audible alarms
Auto-Shutdown Software	PowerChute Personal Edition (via USB and serial interface)
<b>Safety</b>	
Certification/Approvals	FCC Part 15 Class B, TUV, NOM, UL 1778

**APC by Schneider Electric**

132 Fairgrounds Rd  
West Kingston, RI 02892  
Tel: 800-800-4272  
www.apc.com

