

# AR3150

[TAA, BAA\_COTS] APC NetShelter SX, Server Rack Enclosure, 42U, Black, 1991.4H x 750W x 1070D mm



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Product or Component Type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels

## Physical

Height	78.4 in (199.1 cm)
Width	29.5 in (75 cm)
Depth	42.1 in (107 cm)
Net Weight	343.83 lb(US) (155.96 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.02 in (91.49 cm)
Minimum Mounting Depth	10.31 in (26.19 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.6 kg) dynamic 3750 lb(US) (1701.0 kg) static

## Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

## Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304236375
Returnability	No
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	83.3 in (211.7 cm)
Package 1 Width	33.5 in (85.1 cm)
Package 1 Length	45.5 in (115.6 cm)
Package 1 Weight	370.77 lb(US) (168.18 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------