

AR3355

APC NetShelter SX, Server Rack Enclosure, 45U, Black, 2124H x 750W x 1200D mm



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or Component Type	Rack enclosure
Number of rack unit	45U
Provided equipment	Baying hardware Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels

Physical

Height	83.6 in (212.4 cm)
Width	29.5 in (75 cm)
Depth	47.2 in (120 cm)
Net Weight	372.6 lb(US) (169 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	41.3 in (104.8 cm)
Minimum mounting depth	10.31 in (26.19 cm)
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.6 kg) dynamic 3750 lb(US) (1701.0 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304290223
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	88.2 in (224 cm)
Package 1 Width	52.5 in (133.4 cm)
Package 1 Length	33.5 in (85 cm)
Package 1 Weight	415.4 lb(US) (188.4 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------