

Features

- Premium Quality and High Performance Design

Ordering Information

Adapter Type	Color	Number of Ports	UPC Number	Catalog Number
LC Duplex	Aqua	6	662620103730	FSPLCDM6AQ

Listings

TIA-568-C.3
TIA-604-FOCIS

Specifications

Application	Interconnect
Connectivity	Receptacle
Size	5.1" X 1.1"
Material	Phosphor Bronze
Mounting Hardware	Snap-In
Type	6) LC Duplex
Repeatability	0.2 dB
Back Reflection	-25 dB
Service Life	500 matings
Temperature Rating	-40 °C to +85 °C



Performance

Insertion Loss Max	
0.30 dB	Insertion Loss Typical
	0.20 dB

Online Resources

eCatalog