

# OptiChannel Fiber Connector OM3, MM

# HUBBELL

## Features

- Pack of 6 connectors
- Each in a protective capsule with cleave protector, extended dust cap, 900µm boot and splice sleeve
- Compatible with fusion splicers having a removable fiber holder
- Metal holder fixture required (sold separately)
- Hubbell fusion splice heat shrink oven, Catalog Number FCSPHISOVEN is also required for termination



## Ordering Information

Description	Color	Catalog Number	UPC Number
Fiber Optic, Connector, Fusion Splice, FC, OM3, Pre-Polished, 900, Pack of 16	Aqua	<b>FCSCF900M50G6PK</b>	662620315355

## Listings

Telcordia GR-326-CORE  
TIA-568-C.3  
TIA-604-FOCIS

## Performance

Environmental	
Operating temperature	0 °C to 70 °C
Optical	
Insertion loss	0.5dB (0.35dB typical), 0.75dB max
Mating durability	500 cycles, 0.1dB change
Multimode return loss	35dB Typ, 22dB minimum
Singlemode return loss	55dB Typ, 40dB minimum

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions  
Sales Drawing