



SKU: ELT-2

UPC: 0783669257328

Features & Benefits:

Description: Permagraund Copper Grounding E Crimp, Main Conductor Range 2/0-1, Main Rebar Size #3, Tap Range 2/0-1, Tap Rebar Size #3, UL, CSA

Specs

Additional Class Attributes

Fixing Type	NA
ILSCOs Die Index Number	O

Conductor Ranges

Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	2/0 Str - 1 Str
Conductor Range CU Stranded (Secondary, tap, load)	2/0 Str - 1 Str
Rebar Size(s) Main	#3 (3/8)
Rebar Size(s) Secondary	#3 (3/8)

Dimensions

Height (IN)	0.75
Height BX (IN)	2
Length (IN)	1.532
Weight (LB)	0.205
Weight BX (LB)	4.9096
Width (IN)	0.75
Width BX (IN)	5

Material and Finish

Conductor Material	Copper
Connector Finish Material	Bare Copper

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 12

Direct Burial	Yes
Dual Rated	No
NEMA Code	S-573-3
UPC Code	78366925732

Testing Standards

Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL / CULUS Specification	UL 467 Listed

Environment and Temperature

Temperature Rating	NA
--------------------	----

Color

Color	Copper
-------	--------