



SKU: ELT-3

UPC: 0783669257342

Features & Benefits:

Description: Permagraund Copper Grounding E Crimp, Main Conductor Range 250-3/0, Main Rebar Size #4, Tap Range 250-3/0, Tap Rebar Size #4, UL, CSA

Specs

Additional Class Attributes

Fixing Type	NA
ILSCOs Die Index Number	997

Conductor Ranges

Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	250 kcmil - 3/0 Str
Conductor Range CU Stranded (Secondary, tap, load)	250 kcmil - 3/0 Str
Ground Rod Size	1/2
Rebar Size(s) Main	#4 (1/2)
Rebar Size(s) Secondary	#4 (1/2)

Dimensions

Height (IN)	2.063
Height BX (IN)	2
Height (mm)	52.4002
Length (IN)	0.936
Length (mm)	23.7744
Weight (LB)	0.246
Weight BX (LB)	4.6654
Width (IN)	0.9
Width BX (IN)	5
Width (mm)	22.86

Material and Finish

Conductor Material	Copper
Connector Finish	Bare
Material	Copper

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 6
Direct Burial	Yes
Dual Rated	No
NEMA Code	S-573-3
UPC Code	78366925734

Testing Standards

Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL / CULUS Specification	UL 467 Listed

Environment and Temperature

Temperature Rating	NA
--------------------	----

Color

Color	Copper
-------	--------