



**SKU:** ELT-4

**UPC:** 0783669257366

**Features & Benefits:**

**Description:** Permaground Copper Grounding E Crimp, Main Conductor Range 2/0-1, Main Rebar Size #3, Tap Range 2-6, UL, CSA

## Specs

### Additional Class Attributes

Fixing Type	NA
ILSCOs Die Index Number	O

### Conductor Ranges

Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	2/0 Str - 1 Str
Conductor Range CU Stranded (Secondary, tap, load)	2 Str - 6 Str
Rebar Size(s) Main	#3 (3/8)

### Dimensions

Height (IN)	0.75
Height BX (IN)	2
Length (IN)	1.411
Weight (LB)	0.221
Weight BX (LB)	6.47
Width (IN)	0.712
Width BX (IN)	5

### Material and Finish

Conductor Material	Copper
Connector Finish Material	Bare Copper

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 25
Direct Burial	Yes

Dual Rated	No
NEMA Code	S-573-3
UPC Code	78366925736

### Testing Standards

Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL / CULUS Specification	UL 467 Listed

### Environment and Temperature

Temperature Rating	NA
--------------------	----

### Color

Color	Copper
-------	--------