



**SKU:** ELT-6

**UPC:** 0783669257403

**Features & Benefits:**

**Description:**Permaground Copper Grounding E Crimp, Main Conductor Range 500-300, Main Rebar Size #6, Tap Range 250-3/0, Tap Rebar Size #3-#4, UL, CSA

## Specs

### Additional Class Attributes

Fixing Type	NA
ILSCOs Die Index Number	1011

### Conductor Ranges

Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	500 kcmil - 300 kcmil
Conductor Range CU Stranded (Secondary, tap, load)	250 kcmil - 3/0 Str
Ground Rod Size	3/4
Rebar Size(s) Main	#6 (3/4)
Rebar Size(s) Secondary	#4 (1/2)

### Dimensions

Height (IN)	2.672
Height BX (IN)	2
Height (mm)	67.8688
Length (IN)	1.328
Length (mm)	33.7312
Weight (LB)	1.033
Weight BX (LB)	6.268
Width (IN)	0.875
Width BX (IN)	5
Width (mm)	22.225

### Material and Finish

Conductor Material	Copper
Connector Finish	Bare
Material	Copper

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 6
Direct Burial	Yes
Dual Rated	No
NEMA Code	S-573-3
UPC Code	78366925740

### Testing Standards

Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL / CULUS Specification	UL 467 Listed

### Environment and Temperature

Temperature Rating	NA
--------------------	----

### Color

Color	Copper
-------	--------