

SKU: MT-25

UPC: 0783669499605

Features & Benefits:

Description:Manually Operated Compression Tool, Crimping Capacity 4/0-8 AL, 8-250 CU



Specs

Additional Class Attributes

Body Type	Lopper
Compression shape	Single indent
Crimp Style	Single point
For Use With (AL)	ACL, CAN, 2ACL, 2ACN, AS 4/0 thru 8 AWG, ALNS, ALND, ASN, ALNN thru 4/0 AWG
For Use With (CU)	CLN4, CLN9, CLND, CLNF, CLNN, CLNS, CLNU, CLW4, CLW9, CLWD, CLWF, CLWN, CLWS, CSN4, CSN9, CSND, CSNF, CSNN, CSNS, CSW4, CSW9, CSWD, CSWF, CSWN, CSWS, CCL, CRAM
Function	Crimp
Heads Exchangeable	No
Head Style	Open
Operating Pressure	NA
Warranty	NA

Additional Technical Specifications

Crimping Capacity	4/0 - 8 AWG AL
Power Source	Manual

Dimensions

Height (IN)	4.875
Height BX (IN)	3.75
Length (IN)	22.625
Weight (LB)	6.9979
Weight BX (LB)	7.3929
Width (IN)	1.125
Width BX (IN)	6.5

Material and Finish

Handle Insulation	No
Handle Material	Metal
Material	Steel

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 1
NEMA Code	S-575-1
UPC Code	78366949960

Color

Color	Blue
Handle Color	Blue

Testing Standards

Prop65 Compliance

WARNING: Cancer and Reproductive Harm -
www.P65warnings.ca.gov