



SKU: SK-1/0

UPC: 0783669819083

Features & Benefits:

Description: Copper Split Bolt, Conductor Range for Equal Main & Tap
1/0-6 Sol, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Connection	Mechanical
Number of Conductors	1
Number of Poles	1

Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	NA
Conductor Range AL Stranded (Secondary, tap, load)	NA
Conductor Range CU Solid (Primary, run, main, line)	8 Sol
Conductor Range CU Solid (Secondary, tap, load)	8 Sol
Conductor Range CU Stranded (Primary, run, main, line)	1/0 Str - 8 Str
Conductor Range CU Stranded (Secondary, tap, load)	1/0 Str - 8 Str
Conductor Range for Equal Run & Tap ACSR	1 ACSR - 6 ACSR
Conductor Range for Equal Run & Tap Str	1/0 Str - 6 Str
Conductor Range for Equal Run & Tap Sol	1/0 Sol - 6 Sol
Conductor Range for Minimum Tap with Maximum Run	10 Sol
Conductor Range AL Solid (Primary, run, main, line)	8 Sol
Max Conductor Copperweld - Str	3 No. 6

Dimensions

Drive Size Main	3/4
Drive Type Main	External Hex
Height (IN)	0.88
Height BX (IN)	2
Length (IN)	1.64
Weight (LB)	0.144
Weight BX (LB)	8.527
Width (IN)	1.01
Width BX (IN)	6.188
Wire Diameter Range Primary (IN)	0.162 - 0.375

Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	NA

Material	Copper
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Copper

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

Bolt and Screw Sizes

Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	NA
Wire Binding Torque	385

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 50
Direct Burial	No
Dual Rated	No
NEMA Code	S-588-4
UPC Code	78366981908

Testing Standards

CSA File Number	LR-701570
CSA Standard	C22.2 No. 65
Prop65 Compliance	WARNING: Cancer and Reproductive Harm - www.P65warnings.ca.gov
RUS Listed	Yes
UL Control Number	460C
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating	90°C
--------------------	------

Color

Color	Silver
-------	--------

Voltage

Voltage Rating	35 kV
----------------	-------