



**SKU:** ASN-250

**UPC:** 0783669184808

**Features & Benefits:**

**Description:** Surecrimp Aluminum Compression Sleeve, Conductor Size 250, Tin Plated, UL, CSA

## Specs

### Additional Class Attributes

Barrel Marking	Hard
Barrel Type	Standard
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	Yes
Flared End	No
ILSCOs Die Index Number	324
Number of Conductors	1
Sight Window	No
Slotted	No

### Dimensions

Height (IN)	0.924
Height BX (IN)	2.25
Height (mm)	23.4696
Inside Diameter (IN)	0.595
Inside Diameter (mm)	15.113
Length (IN)	3.735
Length (mm)	94.869
Outside Diameter (IN)	0.924
Outside Diameter (mm)	23.4696
Weight (LB)	0.141
Weight BX (LB)	0.8018
Width (IN)	0.924
Width BX (IN)	5
Width (mm)	23.4696

### Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	250 kcmil
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Stranded (Primary, run, main, line)	250 kcmil
Conductor Range AL Solid (Primary, run, main, line)	NA
Expanded Conductor Range	250 kcmil - 1/0 Str
Flex Conductor Range	NA

### Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Material	Aluminum

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 5
Dual Rated	Yes
NEMA Code	S-588-1
UPC Code	78366918480

### Bolt and Screw Sizes

Mounting Bolt/Stud Size	NA
-------------------------	----

### Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

### Environment and Temperature

Temperature Rating	90°C
--------------------	------

### Color

Color	Silver
Color Code	Red

### Voltage

Voltage Rating	35 kV
----------------	-------