



SKU: ASN-350

UPC: 0783669184822

Features & Benefits:

Description: Surecrimp Aluminum Compression Sleeve, Conductor Size 350, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Barrel Marking	Hard
Barrel Type	Standard
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	Yes
Flared End	No
ILSCOs Die Index Number	299
Number of Conductors	1
Sight Window	No
Slotted	No

Dimensions

Height (IN)	1.105
Height BX (IN)	2.25
Height (mm)	28.067
Inside Diameter (IN)	0.72
Inside Diameter (mm)	18.288
Length (IN)	5.125
Length (mm)	130.175
Outside Diameter (IN)	1.105
Outside Diameter (mm)	28.067
Weight (LB)	0.275
Weight BX (LB)	0.84
Width (IN)	1.105
Width BX (IN)	4.25
Width (mm)	28.067

Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	350 kcmil
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Stranded (Primary, run, main, line)	350 kcmil
Conductor Range AL Solid (Primary, run, main, line)	NA
Expanded Conductor Range	350 kcmil - 3/0 Str
Flex Conductor Range	NA

Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 3
Dual Rated	Yes
NEMA Code	S-588-1
UPC Code	78366918482

Bolt and Screw Sizes

Mounting Bolt/Stud Size	NA
-------------------------	----

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating	90°C
--------------------	------

Color

Color	Silver
Color Code	Brown

Voltage

Voltage Rating	35 kV
----------------	-------