

Representative Image

Alternate Catalog No. XT2HU3125BFF000XXX
Catalog No. 1SDA074802R1

Description: XT2H 125TMA 125-625-1250 3PFFUL/CSA

UPC No 8015644787790

Home > Circuit Breakers > Molded Case Circuit Breakers > SACE Tmax XT

C.BREAKER TMAX XT2H 125 UL/CSA FIXED THREE-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMA R 125 I3=625...1250 A

Descriptors

Category	SACE Tmax XT

Specifications

Trip Unit	TMA
Product Main Type	SACE Tmax XT
Frame size	XT2
Extended Product Type	XT2H 125 TMA 125-625..1250 3p FF UL/CSA
Standards	UL
Rated Voltage (V)	600 V
Rated Current	125 A
Interruption Rating	H (65kA @480VAC)
Number of Poles	3

Approvals

Certification	UL