

NON-INSULATED STRANDED CONDUCTOR, COPPER, TINNED, ROPELAY, 250', 115.08 KCMIL

CATALOG NUMBER

LPC126RL250



CERTIFICATIONS



FEATURES

Provides a path to ground for lightning currents

PRODUCT ATTRIBUTES

Certification Details: UL® 96

Material: Copper

Finish: Tinned

UL Conductor Class: Class II

Conductor Type: Ropelay

Number of Wires: 28

Wire Diameter: 0.064"

Diameter: 0.470"

Length: 250'

Cross Section: 115.080 kcmil

Unit Weight: 0.380 lb

ADDITIONAL PRODUCT DETAILS

Unit weight is per foot (0.3048 m).

Cut-to-order (CTO) lengths are available for an additional charge.

Equivalent Conductor Size	
Part Number	Conductor Size
LPC134xxx	2/0
LPC136xxx	3/0
LPC137xxx	4/0

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.